

TECHSPEC® 25mm, 1500mm-∞ Primary WD, HR Series Fixed Focal Length Lens



25mm Focal Length



Stock **#63-782** 10 TO 12 DAYS

- 1 +

₹51,765.00

ADD TO CART

Qty 1+

₹51,765.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
41.07

Horizontal Field of View, 1/2" Sensor:
56.6mm - 14.7°

Horizontal Field of View, 2/3" Sensor:
78mm - 20.2°

Filter Thread: M25.5 x0.50 (Female)
Maximum Diameter (mm): 37.5
Weight (g): 96
Horizontal Field of View, 1/3" Sensor: 42.4mm - 11.1°
Maximum Rear Protrusion (mm): 2.81
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0298
Horizontal Field of View @ Max Sensor Format: 78mm - 20.2°
Number of Elements (Groups): 9 (6)
Horizontal Field of View, 1/1.8" Sensor: 63.8mm - 16.6°
Horizontal Field of View, 1/2.5" Sensor: 51.3mm - 13.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.113
Maximum Sensor Format: 2/3"
Working Distance (mm): 200 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/22
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 17.67
Horizontal Field of View, 1/4" Sensor: 31.8mm - 8.3°
Object Space Principal Plane (mm): 30.53
Image Space Principal Plane (mm): -11.19
Field of View at Max Sensor Format: Horizontal: 78mm - 20.2° Vertical: 58.4mm - 15.2° Diagonal: 97.8mm - 25.1°
Maximum Distortion (%): 0.1
Exit Pupil Position (mm): -38.04
Optimized Working Distance (mm): 1500 - ∞
Lens Wavelength Range: VIS
Imaging Lens Type: High Performance Lens
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View

