

[See all 18 Products in Family](#)

TECHSPEC® 25mm Dia., 0.25 NA, V-Coated 1550nm NIR Aspheric Lens



Stock #22-940 [CONTACT US](#)

[Other Coating Options](#)

- 1 + MRP ₹45,300

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹45,300 each
Qty 6-10	₹40,760 each
Qty 11-25	₹38,036 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.00 +0.0/-0.025 **Diameter (mm):**

Centering (arcmin):

<2.5	
22.5	Clear Aperture CA (mm):
6.43	Edge Thickness ET (mm):
8.50 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:

Optical Properties

50.00 @ 1550nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
42.65 @ 587.6nm	Back Focal Length BFL (mm):
N-SF6	Substrate: <input type="checkbox"/>
1550	Aspheric Design Wavelength (nm):
1550nm V-Coat	Coating:
R _{abs} < 0.25% @ 1550nm @ 0° AOI	Coating Specification:
40-20	Surface Quality:
2	f#:
1550	Design Wavelength DWL (nm):
Infinite	Conjugate Distance:
5 J/cm ² @ 1550nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>
0.4λ RMS and 2λ PV	Asphere Figure Error, @ 632.8nm:
20.00	Power (diopters):

Environmental & Durability Factors

ADHESION AND ABRASION AS PER ML-PRF13830B APP C, PARAC.3.8.4 AND C.3.8.5	Durability:
--	--------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed at 1550nm
- Precision Grade Aspheric Surface
- Uncoated and <0.25% Reflectance V-Coat Options

TECHSPEC® 1550nm Precision Near-Infrared (NIR) Aspheric Lenses are designed at 1550nm to eliminate spherical aberration in the near-infrared. 1550nm lasers are commonly used in telecom, LiDAR, and other applications requiring eye-safe design features. Manufactured from S-TiH6 or N-SF6 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. Featuring a 0.4λ RMS aspheric figure error, these lenses are ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. TECHSPEC® 1550nm Precision Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

;