

[See all 157 Products in Family](#)

TECHSPEC® 25mm Dia 30R/70T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#47-240** **5 In Stock**

⊖ 1 ⊕ MRP ₹15,033

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹15,033 each
Qty 6-25	₹11,703 each
Qty 26-99	₹10,896 each
Need More?	Request Quote

Product Downloads

General

Note:
Beamsplitter-coated side is marked with a black dot

Type:
Standard Beamsplitter

Physical & Mechanical Properties

Clear Aperture (%):

>85	Construction:
Plate	
	Diameter (mm):
25.00	
	Edges:
Cut with 0.25mm maximum edge chip	
	Parallelism (arcmin):
≤3	
	Thickness (mm):
3.00 ±0.25	

Optical Properties

45	Angle of Incidence (°):
	Coating Specification:
	Surface 1: 30/70 ±5% @ 550nm, ±10% @ 400 - 700nm
	Surface 2: AR R _{avg} ≤1%, R _{abs} ≤2% @ 400 - 700nm
30/70	Reflection/Transmission Ratio (R/T):
N-BK7	Substrate: <input type="checkbox"/>
1λ per inch	Surface Flatness (P-V):
60-40	Surface Quality:
400 - 700	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- [C-Mounted Plate Beamsplitters](#) Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification [imaging](#) systems and for combining low power [laser](#) beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.


Technical Information



VIS AR Back-Surface Coating Performance at 45 Degrees



VIS 30R/70T Beamsplitter



Compatible Mounts