

TECHSPEC<sup>®</sup> 25mm Dia., 3mm Thick UV-AR Coated, 1λ Fused Silica Window



Stock #19-853 10 TO 12 DAYS

-

1

+

₹8,265.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹8,265.00                     |
| Qty 6+                        |
| ₹6,612.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Abbe Number (v<sub>d</sub>):  
67.8

Bevel:  
Protective as needed

Clear Aperture (%):  
90

Clear Aperture CA (mm):

|                                                                                                                                                       |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| 22.50                                                                                                                                                 |
| <b>Diameter (mm):</b><br>25.00 +0.00/-0.20                                                                                                            |
| <b>Thickness (mm):</b><br>3.00 ±0.38                                                                                                                  |
| <b>Coating:</b><br>UV-AR (250-425nm)                                                                                                                  |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.0% @ 250 - 425nm<br>R <sub>avg</sub> ≤0.75% @250 - 425nm<br>R <sub>avg</sub> ≤0.5% @ 370 - 420nm |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C)                |
| <b>Density (g/cm³):</b><br>2.20                                                                                                                       |
| <b>Edges:</b><br>Fine Ground                                                                                                                          |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.458                                                                                                    |
| <b>Knoop Hardness (kg/mm²):</b><br>522                                                                                                                |
| <b>Parallelism (arcmin):</b><br><5                                                                                                                    |
| <b>Poisson's Ratio:</b><br>0.16                                                                                                                       |
| <b>Substrate:</b><br><a href="#">Fused Silica</a> (Corning 7980)                                                                                      |
| <b>Surface Quality:</b><br>60-40                                                                                                                      |
| <b>Transmitted Wavefront, P-V:</b><br>1λ                                                                                                              |
| <b>Type:</b><br>Protective Window                                                                                                                     |
| <b>Wavelength Range (nm):</b><br>250 - 450                                                                                                            |
| <b>Young's Modulus (GPa):</b><br>73                                                                                                                   |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>3 J/cm² @ 355nm, 10ns                                                                 |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |