

[See all 8 Products in Family](#)

TECHSPEC® 25mm Dia. 1030nm 45°, Yb:YAG Laser Line Mirror



Yb:YAG ZERODUR Laser Line Mirrors

Stock **#26-897** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹19,383

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹19,383 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

4.00 +/-0.2 **Thickness (mm):**

25.00 +/-0.00/-0.20 **Diameter (mm):**

90 **Clear Aperture (%):**

Optical Properties

ZERODUR®

Substrate: □

20-10

Surface Quality:

45

Angle of Incidence (°):

Laser Mirror (1030nm)

Coating:

1030

Design Wavelength DWL (nm):

99.8

Reflection at DWL (%):

1020 - 1040

Wavelength Range (nm):

λ/10

Surface Flatness (P-V):

Coating Specification:

$R_{abs} > 99.80\%$ @ 1030nm @ 45° AOI $R_{avg} > 99.5\%$
@ 1020 - 1040nm @ 45° AOI

Dielectric

Coating Type:

Damage Threshold, By Design: □

20 J/cm² @ 1030nm, 20ns, 20Hz

Regulatory Compliance

[View](#)

Certificate of Conformance:

United States

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Yb:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Yb:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ these mirrors are great for applications where the optics will be exposed to fluctuating temperatures. The Yb:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Yb:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering.