

[See all 130 Products in Family](#)

TECHSPEC<sup>®</sup> 25mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC<sup>®</sup> Nd:YAG Laser Line Mirrors



Stock **#45-991** **20+ In Stock**

-

1

+

₹12,378

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹12,378 each                  |
| Qty 6-25       | ₹10,899 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

<3Parallelism (arcmin):

Clear Aperture (%):

|                                                                                                                        |                                     |
|------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| >90                                                                                                                    |                                     |
| Ground                                                                                                                 | Back Surface:                       |
| 25.00 +0.00/-0.20                                                                                                      | Diameter (mm):                      |
| 6.00 ±0.20                                                                                                             | Thickness (mm):                     |
| Optical Properties                                                                                                     |                                     |
| 10-5                                                                                                                   | Surface Quality:                    |
| 99.8                                                                                                                   | Reflection at DWL (%):              |
| Coating Specification:<br>R <sub>abs</sub> >99.8% @ 532nm @ 45° AOI<br>R <sub>avg</sub> >99.5% @ 523 - 537nm @ 45° AOI |                                     |
| 523 - 537                                                                                                              | Wavelength Range (nm):              |
| λ/10                                                                                                                   | Surface Flatness (P-V):             |
| Dielectric                                                                                                             | Coating Type:                       |
| Laser Mirror (532nm)                                                                                                   | Coating:                            |
| 532                                                                                                                    | Design Wavelength DWL (nm):         |
| 45                                                                                                                     | Angle of Incidence (°):             |
| Fused Silica (Corning 7980)                                                                                            | Substrate: <input type="checkbox"/> |
| Damage Threshold, Reference: <input type="checkbox"/><br>15 J/cm² @ 532nm, 20ns, 20Hz                                  |                                     |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | REACH 241:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
  - High Laser Induced Damage Threshold Specifications
  - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
  - TECHSPEC® Laser Mirror Substrates and TECHSPEC® Yb:YAG Laser Line Mirrors Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts