


TECHSPEC[®] 25mm Dia., 532nm, Stemmed Laser Mirror



Stock #17-557 CLEARANCE CONTACT US

-

1

+

₹15,051.00

ADD TO CART

Qty 1-5
₹15,051.00
Qty 6+
₹12,050.00
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
22.50

Coating:
Laser Mrror (532nm)

Design Wavelength DWL (nm): 532
Diameter (mm): 25.00 +0.00/-0.10
Substrate: Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Clear Aperture (%): 90.00
Back Surface: Commercial Polish
Coating Specification: R_{abs} >99.8% @ 532nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Damage Threshold, Reference: 10J/cm² @ 20ns, 20Hz @ 532nm
Edges: Ground, protective bevel as needed
Stem Diameter (mm): 12.50 +0.00/-0.10
Compatible Kinematic Mount: #58-853
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View