

## 25mm Dia., 488nm Laser Line Longpass Filter



Laser Line Longpass Filters

Stock **#47-503** **1 In Stock**

⊖ 1 ⊕ ₹59,789

**ADD TO CART**

Volume Pricing	
Qty 1+	₹59,789 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Longpass Filter **Type:**

**Angle Tuning Range, for 0 - 8° Shift:**  
-0.3% of Laser Wavelength

Bandwidth (nm): >600 **Note:**

### Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**

22	Clear Aperture CA (mm):
±0.1	Thickness Tolerance (mm):
88	Clear Aperture (%):

## Optical Properties

0 ±2	Angle of Incidence (°):
>600	Bandwidth (nm):
394 - 488	OD 6 Blocking Wavelength Range (nm):
≥6.0	Optical Density OD (Average):
488	Design Wavelength DWL (nm):
<a href="#">Fused Silica</a> (Corning 7980)	Substrate: <input type="checkbox"/>
Hard Coated	Coating:
60-40	Surface Quality:
93.00	Transmission (%):
494.3 - 1100.8	Transmission Wavelength (nm):
2.40	Edge Steepness (nm):
<4.9	Transition Width (nm):
488	Laser Blocking Wavelength (nm):
0.5 J/cm <sup>2</sup> @ 266nm, 10ns, 10Hz 1 J/cm <sup>2</sup> @ 532nm, 10ns, 10Hz	Damage Threshold, By Design: <input type="checkbox"/>

## Threading & Mounting

3.5	Mount Thickness (mm):
-----	-----------------------

## Environmental & Durability Factors

Environmental: ML-STD-810F, Physical: ML-C-48497A	Durability:
<5	Temperature Dependence (ppm/°C):

## Regulatory Compliance


<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 209:
<a href="#">View</a>	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

## Product Details

- Up to 93% Transmission to Detect Weak Signals
- Deep > OD 6 Blocking for Maximum Laser Rejection
- Ideal for Raman Spectroscopy, Confocal Microscopy, and Biotech Instrumentation
- Unrivaled Performance and Lifetime

Our Laser Line Longpass filters offer unprecedented performance in longpass laser edge filter applications. The steep edges (measured from an optical density of 6.0 to a transmission of 50%) make it possible to measure even the smallest Raman shifts, making these filters a superior alternative to costly holographic notch filters for Stokes Raman scattering measurements. Compared to notch filters, these edge filters offer better transmission, higher laser line blocking, and steeper edges, permitting measurement of Raman signals extremely close to the laser line. The large bandwidths and exceptional transmission permit these filters to be used in even the most demanding imaging applications.

## Technical Information



## Compatible Mounts

---