

TECHSPEC® 25mm Dia., 4mm Thick NIR I Coated, 1λ Fused Silica Window



Stock #19-864

10 TO 12 DAYS

-

1

+

₹8,048.00

ADD TO CART

Qty 1-5

₹8,048.00

Qty 6+

₹6,438.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):

67.8

Bevel:

Protective as needed

Clear Aperture (%):

90

Clear Aperture CA (mm):

22.50
Diameter (mm): 25.00 +0.00/-0.20
Thickness (mm): 4.00 ±0.38
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 60-40
Transmitted Wavefront, P-V: 1λ
Type: Protective Window
Wavelength Range (nm): 600 - 1050
Young's Modulus (GPa): 73
Damage Threshold, Reference: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant