


[See all 9 Products in Family](#)

TECHSPEC® 25mm Dia x 12.5mm FL Uncoated, Si Aspheric Lens



Stock **#89-357 1 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹52,938

ADD TO CART

Volume Pricing	
Qty 1-5	₹52,938 each
Qty 6+	₹42,506 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

≤10 **Centering (arcmin):**

Centering, ETD (µm):

<21.8	Clear Aperture CA (mm):
22.5	
	Edge Thickness ET (mm):
2.37	
	Center Thickness CT (mm):
4.75 ±0.10	
	Bevel:
Protective as needed	
	Edges:
Diamond Turned	
	Shape of Back Surface:
Concave	

Optical Properties

	Effective Focal Length EFL (mm):
12.50 @4000nm	
	Numerical Aperture NA:
1.00	
	Back Focal Length BFL (mm):
10.70	
	Substrate: <input type="checkbox"/>
Silicon (Si)	
	Aspheric Design Wavelength (nm):
4000	
	Asphere Figure Error, RMS @ 632.8nm:
λ/6	
	Coating:
Uncoated	
	Surface Accuracy, P-V (μm):
<0.3	
	Surface Quality:
60-40	
	f##:
0.5	
	Radius R₂ (mm):
87.361	
	Wavelength Range (nm):
1200 - 7000	
	Conjugate Distance:
Infinite	

Regulatory Compliance

	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Diffraction-Limited Performance
- Low Density and Dispersion
- Ideal for Weight Sensitive IR Applications
- Available with BBAR (1650-3000nm) or Mid-Wave Infrared (3000-5000nm) AR Coatings

TECHSPEC® Silicon Aspheric Lenses are high performance, lightweight solutions for BBAR and Mid-Wave Infrared (MMIR) applications and are ideal alternatives for costly ZnSe lenses and brittle Germanium lenses. These lenses are available with efficient broadband AR coatings for the BBAR (1650-3000nm) or MMIR (3000-5000nm) spectral regions. TECHSPEC Silicon Aspheric Lenses feature the mechanical and thermal properties required to withstand many of the effects of harsh environments including fluctuations in temperature and pressure. Because silicon is a low density material, these lenses are also ideal for weight-sensitive systems, such as those found in many defense applications.

Compatible Mounts