

TECHSPEC[®] 25mm Dia. x 125mm FL, Uncoated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#48-298** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹10,614.00

ADD TO CART

Qty 1-5

₹10,614.00

Qty 6+

₹8,483.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Back Focal Length BFL (mm):

123.82
Effective Focal Length EFL (mm): 125.00
Coating: Uncoated
Coating Specification: Uncoated
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.42 ±0.10
Edge Thickness ET (mm): 2.05
Radius R ₁ =R ₂ (mm): 114.08
Clear Aperture CA (mm): 24.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View