

[See all 27 Products in Family](#)

TECHSPEC[®] 25mm Dia. x 150mm FL, Uncoated, Si Plano-Convex Lens



Stock **#69-680** **13 In Stock**
[Other Coating Options](#)

-

1

+

₹17,438

ADD TO CART

Volume Pricing	
Qty 1-5	₹17,438 each
Qty 6-25	₹13,935 each
Qty 26-49	₹13,079 each
Need More?	Request Quote

Product Downloads

General	
Plano-Convex Lens	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
<3	Centering (arcmin):

3.00 ±0.10	Center Thickness CT (mm):
2.78	Edge Thickness ET (mm):
24	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
150.00 @ 10.6µm	Effective Focal Length EFL (mm):
149.12	Back Focal Length BFL (mm):
Uncoated	Coating:
Silicon (Si)	Substrate: □
60–40	Surface Quality:
2λ	Power (P-V) @ 632.8nm:
λ/2	Irregularity (P-V) @ 632.8nm:
362.64	Radius R ₁ (mm):
6.00	f#:
0.08	Numerical Aperture NA:
1200 - 7000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Wavelength Range of 1.2 - 7µm
- Low Density and Dispersion
- Focal Lengths of 25 – 250mm Available
- Additional [Infrared Lenses](#) Available in Popular Substrates

Our TECHSPEC® Silicon Plano-Convex (PCX) Lenses feature precision polished surfaces, making them ideal for a variety of infrared applications, including Near-Infrared (NIR) imaging, and infrared spectroscopy. Available in a variety of focal lengths from f/1 thru f/10, the lenses are offered uncoated or broadband anti-reflection coated. For more information on Silicon properties, please review our guide to selecting [The Correct Material for Infrared \(IR\) Applications](#).

Technical Information



Compatible Mounts

;