

**TECHSPEC® 25mm Dia. x 100mm FL, YAG-BBAR Coated, Achromatic Lens**



YAG-BBAR Coated Achromatic Lenses



Stock #33-211 **20+ In Stock**

[Other Coating Options](#)

1 MRP ₹12,914

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹12,914 each
Qty 6-25	₹10,291 each
Qty 26-49	₹9,635 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Achromatic Lens **Type:**

**Physical & Mechanical Properties**

25.00 +0.000/-0.025	<b>Diameter (mm):</b>
24.00	<b>Clear Aperture CA (mm):</b>
<1	<b>Centering (arcmin):</b>
8.50 ±0.20	<b>Center Thickness CT (mm):</b>
6.00 ±0.10	<b>Center Thickness CT 1 (mm):</b>
2.5 ±0.10	<b>Center Thickness CT 2 (mm):</b>
6.61	<b>Edge Thickness ET (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

100.00	<b>Effective Focal Length EFL (mm):</b>
±1	<b>Focal Length Tolerance (%):</b>
95.92	<b>Back Focal Length BFL (mm):</b>
587.6	<b>Focal Length Specification Wavelength (nm):</b>
61.47	<b>Radius R<sub>1</sub> (mm):</b>
44.64	<b>Radius R<sub>2</sub> (mm):</b>
129.94	<b>Radius R<sub>3</sub> (mm):</b>
<a href="#">N-BK7 / N-SF5</a>	<b>Substrate:</b> <input type="checkbox"/>
40-20	<b>Surface Quality:</b>
4.00	<b>f#:</b>
0.12	<b>Numerical Aperture NA:</b>
YAG-BBAR (500-1100nm)	<b>Coating:</b>
R <sub>abs</sub> <0.25% @ 532nm R <sub>abs</sub> <0.25% @ 1064nm R <sub>avg</sub> <1.0% @ 500 - 1100nm	<b>Coating Specification:</b>
1.5λ	<b>Power (P-V) @ 632.8nm:</b>
M4	<b>Irregularity (P-V) @ 632.8nm:</b>
500 - 1100	<b>Wavelength Range (nm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 219:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:


- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Optimized for <0.25% Absolute Reflectivity at 532nm and 1064nm
- Excellent Broadband Transmission from 500 - 1100nm
- Low Cost Alternative to Air-Spaced Focusing Doublets

TECHSPEC® YAG-BBAR Coated Achromatic Lenses consist of two optical components cemented together to form a doublet that is ideal for correcting on-axis spherical and chromatic aberrations. These achromats feature a broadband anti-reflective coating with superior transmission from 500 - 1100nm, and are optimized for less than 0.25% absolute reflectivity at 532 and 1064nm. Our TECHSPEC® YAG-BBAR Coated Achromatic Lenses are specifically designed to minimize the spot size for polychromatic illumination within the recommended usable wavelength range, but may also be used for focusing Nd:YAG lasers, especially those with an alignment beam.



## Compatible Mounts