

TECHSPEC® 25mm Dia. x 150mm FL, YAG-BBAR Coated, Achromatic Lens



YAG-BBAR Coated Achromatic Lenses



Stock **#33-212** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹9,657.00

ADD TO CART

Qty 1-5

₹9,657.00

Qty 6+

₹7,721.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.000/-0.025

Effective Focal Length EFL (mm):

150.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 146.1
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 7.90 ±0.20
Center Thickness CT 1 (mm): 5.7 ±0.10
Center Thickness CT 2 (mm): 2.2 ±0.10
Radius R ₁ (mm): 91.37
Radius R ₂ (mm): 66.21
Radius R ₃ (mm): 197.71
Edge Thickness ET (mm): 6.65
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 6.00
Numerical Aperture NA: 0.08
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 500 - 1100

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View