

[See all 47 Products in Family](#)

TECHSPEC® 25mm Dia. x 35mm FL, NIR II Coated, Achromatic Lens



Stock **#45-800** [CONTACT US](#)

[Other Coating Options](#)

1 MRP ₹15,134

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹15,134 each
Qty 6-25	₹12,107 each
Qty 26-49	₹11,401 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.0/-0.025

24.00 **Clear Aperture CA (mm):**

<1 **Centering (arcmin):**

15.00 ±0.20 **Center Thickness CT (mm):**

11.00 ±0.10 **Center Thickness CT 1 (mm):**

4.00 ±0.10 **Center Thickness CT 2 (mm):**

10.48 **Edge Thickness ET (mm):**

Protective as needed **Bevel:**

Optical Properties

35.00 **Effective Focal Length EFL (mm):**

±1 **Focal Length Tolerance (%):**

26.87 **Back Focal Length BFL (mm):**

880.00 **Focal Length Specification Wavelength (nm):**

23.40 **Radius R₁ (mm):**

-20.11 **Radius R₂ (mm):**

-87.52 **Radius R₃ (mm):**

Substrate:
N-LAK22 / N-SF6

40-20 **Surface Quality:**

1.4 **f#:**

0.36 **Numerical Aperture NA:**

NIR II (750-1550nm) **Coating:**

Coating Specification:
R_{abs} ≤1.5% @ 750 - 800nm
R_{abs} ≤1.0% @ 800 - 1550nm
R_{avg} ≤0.7% @ 750 - 1550nm

1.5λ **Power (P-V) @ 632.8nm:**

M4 **Irregularity (P-V) @ 632.8nm:**

750 - 1550 **Wavelength Range (nm):**

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 240:
Compliant

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:


- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Designed to Give Increased Resolution and Smaller Spot Sizes for NIR Wavelengths (750-1100nm)
- Decreased Spherical Aberration for Monochromatic Sources Out to 2 μ m
- Broadband AR Coating has <1% Reflectivity Between 750–1550nm

TECHSPEC® Near-IR (NIR) Achromatic Lenses are designed to provide the smallest spot size possible for polychromatic light between 750 and 1100nm. By utilizing our NIR doublets instead of standard doublets designed for the visible, the RMS spot diameter can be reduced from 43 μ m to 22.5 μ m, for example, when using polychromatic light. Spot size will be smaller when focusing on monochromatic sources. TECHSPEC Near-IR (NIR) Achromatic Lenses also reduce spherical aberration and perform superior when used with a monochromatic source up to 2 μ m in wavelength. Typical applications for these doublets include imaging lenses for the near infrared, focusing and expanding of NIR lasers, and focusing/collimating lenses for fiber optics and NIR LEDs.

Technical Information



NIR AR Coatings



Compatible Mounts