

TECHSPEC[®] 25mm Dia. x 200mm FL, NIR I Coated, Achromatic Lens



Stock #22-496 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹11,310.00

ADD TO CART

Qty 1-5
₹11,310.00
Qty 6+
₹9,048.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
200.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 193.761
Focal Length Specification Wavelength (nm): 880.00
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 10.00 ±0.20
Center Thickness CT 1 (mm): 6.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 112.88
Radius R₂ (mm): -112.88
Radius R₃ (mm): -1415.62
Edge Thickness ET (mm): 9.25
Substrate: ☐ N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 8.00
Numerical Aperture NA: 0.06
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 600 - 1050

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View