

TECHSPEC® 25mm Dia. x 45mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-355-INK** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹11,136.00**

ADD TO CART

Qty 1-5
₹11,136.00
Qty 6+
₹8,918.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
45.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 39.28
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 10.89 ±0.20
Center Thickness CT 1 (mm): 7.89 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R₁ (mm): 28.75
Radius R₂ (mm): -21.38
Radius R₃ (mm): -82.92
Edge Thickness ET (mm): 7.08
Substrate: ☐ N-SK11 / N-SF5
Surface Quality: 40-20
f/#: 1.8
Numerical Aperture NA: 0.28
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View