

TECHSPEC® 25mm Dia. x 25mm EFL Precision Aspherized Achromatic Lens



Stock #85-302 **6 In Stock**

- 1 + MRP ₹1,34,385

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,34,385 each
Qty 6-25	₹1,21,169 each
Qty 26-49	₹1,17,840 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**

22.5 **Clear Aperture CA (mm):**

≤3	Centering (arcmin):
25.00	Center Thickness CT (mm):
17.00	Center Thickness CT 1 (mm):
8.0	Center Thickness CT 2 (mm):
16.92	Edge Thickness ET (mm):

Optical Properties

25.00	Effective Focal Length EFL (mm):
16.40	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
N-PK51 / S-NPH2	Substrate: <input type="checkbox"/>
20-10	Surface Quality:
1.00	f#:
0.50	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤ 1.75% @ 400 - 700nm	Coating Specification:
450 - 700	Wavelength Range (nm):
0.8λ	Asphere Figure Error, RMS @ 632.8nm:

Regulatory Compliance


View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details


- All Glass Color-Corrected Asphere
- Ideal for Imaging and Biotech Applications
- MgF₂ Coated

Featuring an all glass design, TECHSPEC® Precision Aspherized Achromatic Lenses are truly achromatic, with less than 10μm of lateral chromatic aberration. These achromatic lenses are diffraction limited over the full visible spectrum, and have high numerical apertures for increased light throughput and small spot sizes. TECHSPEC® Precision Aspherized Achromatic Lenses are ideal for fluorescence microscopy, low signal-to-noise imaging applications, and multiple laser biotech applications.

Technical Information



CT: Center Thickness, ET: Edge Thickness, R: Radius, P: Principal Plane, BFL: Back Focal Length, EFL: Effective Focal Length



Coating Curves
