


TECHSPEC[®] 25mm Dia x 25mm FL Uncoated, Si Aspheric Lens



Stock #89-358 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹46,321

ADD TO CART

Qty 1-5

₹46,321

Qty 6+

₹37,057

Volume Pricing

[Request Quote](#)

Product Downloads

SPECIFICATIONS

General

Aspheric Lens

Type:

Physical & Mechanical Properties	
25.00 +0.00/-0.10	Diameter (mm):
≤10	Centering (arcmin):
<21.8	Centering, ETD (μm):
22.5	Clear Aperture CA (mm):
2.44	Edge Thickness ET (mm):
3.80 ±0.10	Center Thickness CT (mm):
Protective bevel as needed	Bevel:
Diamond Turned	Edges:
Concave	Shape of Back Surface:

Optical Properties	
25.00 @ 4000nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
22.50	Back Focal Length BFL (mm):
Silicon (Si)	Substrate:
4000	Aspheric Design Wavelength (nm):
λ/6	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:
<0.3	Surface Accuracy, P-V (μm):
60-40	Surface Quality:
1.00	f/#:
43.582	Radius R ₂ (mm):
1200 - 7000	Wavelength Range (nm):
Infinite	Conjugate Distance:

Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- Diffraction-Limited Performance
- Low Density and Dispersion
- Ideal for Weight Sensitive IR Applications
- Available with BBAR (1650-3000nm) or Mid-Wave Infrared (3000-5000nm) AR Coatings

TECHSPEC® Silicon Aspheric Lenses are high performance, lightweight solutions for BBAR and Mid-Wave Infrared (MMIR) applications and are ideal alternatives for costly ZnSe lenses and brittle Germanium lenses. These lenses are available with efficient broadband AR coatings for the BBAR (1650-3000nm) or MMIR (3000-5000nm) spectral regions. TECHSPEC Silicon Aspheric Lenses feature the mechanical and thermal properties required to withstand many of the effects of harsh environments including fluctuations in temperature and pressure. Because silicon is a low density material, these lenses are also ideal for weight-sensitive systems, such as those found in many defense applications.

COMPATIBLE MOUNTS