

TECHSPEC®

25mm Dia. x 60mm FL, Uncoated, UV Double-Convex Lens



Stock #48-295 **20+ In Stock** [Other Coating Options](#)

1 MRP ₹14,125

Price inclusive of all taxes

ADD TO CART

UV Fused Silica Double-Convex (DCX) Lenses



Volume Pricing	
Qty 1-5	₹14,125 each
Qty 6-25	₹11,300 each
Qty 26-49	₹10,694 each
Need More?	Request Quote

Product Downloads

- STEP:step PDF Drawing:pdf
- ISO 10110 Drawing
- IGES:igs Zemax:zar
- Zemax:zmx eDrawing:eprt
- Code V:seq EO Spec Sheet
- [Download All](#)

General

Type: Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm): 25.00 +0.0/-0.025

Centering (arcmin): <1

Bevel: Protective as needed

Center Thickness CT (mm): 5.52 ±0.10

Edge Thickness ET (mm): 2.59

Clear Aperture CA (mm): 24.00

Optical Properties

Back Focal Length BFL (mm): 58.08

Effective Focal Length EFL (mm): 60.00

Coating: Uncoated

Coating Specification: Uncoated

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 40-20

Power (P-V) @ 632.8nm: 1.5λ

Irregularity (P-V) @ 632.8nm: λ/4

Radius R₁=-R₂ (mm): 54.14

f/#: 2.4

Focal Length Specification Wavelength (nm): 587.6

Focal Length Tolerance (%): ±1

Numerical Aperture NA: 0.21

Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 219: **Compliant**

Certificate of Conformance: **View**

Country of Origin: Japan

Imported By: Edmund Optics India Private Limited
267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate

TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.

Technical Information

UV FS Transmission Curve


Uncoated Fused Silica Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

Fused Silica with MgF₂ Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-AR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-VIS Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$

$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$


$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$

$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with VIS 0° Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS 0° (425–675nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with YAG-BBAR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500–1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}$$


$$R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}$$

$$R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with NIR I Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with NIR I (600 – 1050nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

- $R_{abs} \leq 1.5\%$ @ 750 - 800nm
- $R_{abs} \leq 1.0\%$ @ 800 - 1550nm
- $R_{avg} \leq 0.7\%$ @ 750 - 1550nm

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)


Related Products




UV Fused Silica Aspheric Lenses



Uncoated Double-Convex (DCX) Lenses



UV Fused Silica Plano-Convex (PCX) Lenses - Uncoated



Laser Grade Plano-Convex (PCX) Lenses

Frequently Purchased Together



#34-519 - 30.8mm Motorizable Iris Spur Gear
₹2,095

Qty



#34-291 - 22mm Max Aperture Motorizable Iris
₹11,098

Qty



#34-517 - 10.8mm Motorizable Iris Spur Gear
₹1,287

Qty










































#34-293 - 28mm Max Aperture Motorizable Iris
₹11,603

Qty

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	25.0/25.4mm Optic Dia., SM1 Thin Mount, M4	Fixed		#13-787	₹2,119 Request Quote	2 In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
 	25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32	Fixed		#13-788	₹2,119 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0mm Optic Dia., Optic Mount	Fixed		#64-560	₹3,305 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25mm Thin Inner Single Optic Mount	Fixed		#38-755	₹4,137 Request Quote	5 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., L-Slot Direct Mount	Fixed		#36-410	₹6,861 Request Quote	9 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., Side Flange Direct Mount	Fixed		#36-414	₹7,164 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25/25.4mm Diameter, T-Mount Thin Optic Mount	Fixed		#52-292	₹7,264 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25mm Thin Inner Pair Optic Mounts	Fixed		#11-052	₹8,122 Request Quote	3 In Stock <input type="text" value="1"/> 
 	25mm Thick Inner Pair Optic Mounts	Fixed		#11-054	₹8,122 Request Quote	11 In Stock <input type="text" value="1"/> 
 	25/25.4mm Diameter, C-Mount Thin Optic Mount	Fixed		#56-353	₹9,989 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., L-Slot and Rotation Direct Mount	Adjustable - Rotary		#36-411	₹10,291 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-956	₹27,846 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-959	₹54,481 Request Quote	6 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-776	₹76,173 Request Quote	2 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Trending in Optics
- FAQ

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

APPLICATION NOTE

Understanding Optical Specifications

Glossary

Video

 APPLICATION NOTE

Lens Geometry
Performance
Comparison

 APPLICATION NOTE

UV vs. IR
Grade Fused
Silica

 TECHNICAL TOOL

SAG Calculator

[View More](#)