

TECHSPEC®

25mm Dia. x 75mm FL, Uncoated, Si Plano-Convex Lens



Stock **#69-678**

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹17,438

ADD TO CART

Qty 1-5
₹17,438
Qty 6+
₹13,935
Volume Pricing
Request Quote

Product Downloads

SPECIFICATIONS

General

Plano-Convex Lens


Type:

Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
<3	Centering (arcmin):
3.00 ±0.10	Center Thickness CT (mm):
2.57	Edge Thickness ET (mm):
24	Clear Aperture CA (mm):
Protective bevel as needed	Bevel:
Optical Properties	
75.00 @ 10.6µm	Effective Focal Length EFL (mm):
74.12	Back Focal Length BFL (mm):
Uncoated	Coating:
Silicon (Si)	Substrate: ☐
60-40	Surface Quality:
2λ	Power (P-V) @ 632.8nm:
λ/2	Irregularity (P-V) @ 632.8nm:
181.32	Radius R ₁ (mm):
3.00	f/#:
0.17	Numerical Aperture NA:
1200 - 7000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

PRODUCT DETAILS

- Wavelength Range of 1.2 - 7µm
 - Low Density and Dispersion
 - Focal Lengths of 25 – 250mm Available
 - Additional [Infrared Lenses](#) Available in Popular Substrates
- Our TECHSPEC® Silicon Plano-Convex (PCX) Lenses feature precision polished surfaces, making them ideal for a variety of infrared applications, including Near-Infrared (NIR) imaging, and infrared spectroscopy. Available in a variety of focal lengths from f/1 thru f/10, the lenses are offered uncoated or broadband anti-reflection coated. For more information on Silicon properties, please review our guide to selecting [The Correct Material for Infrared \(IR\) Applications](#).

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS