

[See all 105 Products in Family](#)

**TECHSPEC® 25mm Dia x -50mm FL NIR I Coated, Illumination Grade PCV Cylinder Lens**



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#69-823** **5 In Stock**

⊖ 1 ⊕ ₹7,084

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹7,084 each
Qty 6-25	₹6,384 each
Qty 26-49	₹6,072 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cylinder Lens, Plano-Concave **Type:**

**Physical & Mechanical Properties**

25.00 +0.0/-0.2 **Diameter (mm):**

3.00 **Center Thickness CT (mm):**

Center Thickness Tolerance (mm): ±0.1  
Edge Thickness ET (mm): 6.21

## Optical Properties

Effective Focal Length EFL (mm): -50.00

Substrate:  N-BK7

f#: 2.00

Numerical Aperture NA: 0.25

Coating: NIR I (600-1050nm)

Wavelength Range (nm): 600 - 1050

Back Focal Length BFL (mm): -51.97

Coating Specification:  $R_{avg} \leq 0.5\%$  @ 600 - 1050nm

Focal Length Tolerance (%): ±3

Radius  $R_1$  (mm): -25.93

Surface Quality: 60-40

Damage Threshold, By Design:   
7 J/cm<sup>2</sup> @ 1064nm, 10ns

## Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Reach 235: [Compliant](#)

Country of Origin: China

Imported By: Edmund Optics India Private Limited


## Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
- Circular and Rectangular Form Factors
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.

The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---