

[See all 12 Products in Family](#)

TECHSPEC® 25mm Dia. x 50mm EFL, Uncoated, Precision Laser Aspheric Lens



Stock **#24-068** **20+ In Stock**

- 1 + MRP ₹63,864

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹63,864 each
Qty 6-25	₹54,481 each
Qty 26-49	₹48,125 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

25.00 +0.000 / -0.025	Diameter (mm):
22.5	Clear Aperture CA (mm):
3.82	Edge Thickness ET (mm):
7.20 +0.000 / -0.10	Center Thickness CT (mm):

Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
50.00 @ 355nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
45.1	Back Focal Length BFL (mm):
Fused Silica	Substrate: <input type="checkbox"/>
$\lambda/2$ RMS and 2.5 λ PV	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:
20-10	Surface Quality:
2	f#:
355	Design Wavelength DWL (nm):
200 - 2200	Wavelength Range (nm):
Infinite	Conjugate Distance:
0.35 μ m/mm per 1mm Window	Slope Error Aspheric Side:
<2.5	Beam Deviation @ 587.6nm (arcmin):
20.00	Power (diopters):

Regulatory Compliance	
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Diffraction Limited at Designed Nd:YAG Laser Wavelengths
- Laser Damage Designed Coatings on UV Fused Silica Substrates
- Specified Slope Error to Guarantee Low Mid-Spatial Frequency Errors
- [High Precision Laser Grade Aspheric Lenses](#) are also Available

TECHSPEC® Precision Laser Aspheric Lenses are designed to maximize performance in high power laser applications. Featuring diffraction limited performance at their designed wavelengths these aspheric lenses are available with high laser damage threshold coatings optimized at the most common Nd:YAG laser wavelengths. With a $\lambda/2$ aspheric surface figure and 0.35 μ m/mm slope error, TECHSPEC® Precision Laser Aspheric Lenses minimize the mid-spatial frequency (MSF) errors and are ideal for integration into demanding laser processing, cutting, and additive manufacturing applications. Featuring UV fused silica substrates, these aspheres are highly durable and resistant to thermal expansion.