

[See all 26 Products in Family](#)

TECHSPEC<sup>®</sup> 25mm Dia. x -50mm FL, VIS 0°, Inked, Double-Concave Lens



Stock **#47-918-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

₹5,085

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹5,085 each                   |
| Qty 10-25      | ₹4,590 each                   |
| Qty 26-49      | ₹4,073 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Concave Lens

Physical & Mechanical Properties

Diameter (mm):

25.00 ±0.025


|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Protective as needed                 | Bevel:                                      |
| 2.50                                 | Center Thickness CT (mm):                   |
| ±0.10                                | Center Thickness Tolerance (mm):            |
| <1                                   | Centering (arcmin):                         |
| 24.00                                | Clear Aperture CA (mm):                     |
| 5.40                                 | Edge Thickness ET (mm):                     |
| Optical Properties                   |                                             |
| -50.00                               | Effective Focal Length EFL (mm):            |
| N-BK7                                | Substrate: □                                |
| 2.00                                 | f/#:                                        |
| 0.25                                 | Numerical Aperture NA:                      |
| VIS 0° (425-675nm)                   | Coating:                                    |
| 425 - 675                            | Wavelength Range (nm):                      |
| -50.82                               | Back Focal Length BFL (mm):                 |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                      |
| 587.6                                | Focal Length Specification Wavelength (nm): |
| ±1                                   | Focal Length Tolerance (%):                 |
| -52.10                               | Radius R <sub>1</sub> =R <sub>2</sub> (mm): |
| 40-20                                | Surface Quality:                            |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, By Design: □              |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
| Regulatory Compliance                |                                             |
| View                                 | Certificate of Conformance:                 |
| Japan                                | Country of Origin:                          |
| Edmund Optics India Private Limited  | Imported By:                                |

## Product Details

- AR Coated to Provide <0.4% Reflectance per Surface for 425 - 675nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are best used in 0° angle of incidence situations and provide optimized transmission in the 425nm – 675nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS-NIR](#), [NIR I](#), or with [NIR II](#) AR coating options.

## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts