


TECHSPEC®

25mm Dia x -75mm FL Negative Doublet Lens MgF₂ Coated



Stock #45-422 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹9,396.00

ADD TO CART

Qty 1-5
₹9,396.00
Qty 6+
₹7,526.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-75.00

Focal Length Tolerance (%):
±1

Back Focal Length BFL (mm): -77.65
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 6.56 ±0.20
Center Thickness CT 1 (mm): 2.50 ±0.10
Center Thickness CT 2 (mm): 4.06 ±0.10
Radius R₁ (mm): -46.07
Radius R₂ (mm): 36.65
Radius R₃ (mm): 108.00
Edge Thickness ET (mm): 8.90
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View