

[See all 6 Products in Family](#)

**TECHSPEC® 25mm Dia. x 50mm FL, Uncoated, 266nm DWL, CaF<sub>2</sub> Aspheric Lens**



TECHSPEC® Calcium Fluoride (CaF<sub>2</sub>) Aspheric Lenses

Stock **#13-464** [CONTACT US](#)

- 1 + MRP ₹58,012

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹58,012 each
Qty 6-25	₹51,959 each
Qty 26-49	₹46,107 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.10 **Diameter (mm):**

**Centering (arcmin):**

<1

22.50 **Clear Aperture CA (mm):**

5.09 **Edge Thickness ET (mm):**

8.50 ±0.10 **Center Thickness CT (mm):**

Diamond Turned **Edges:**

## Optical Properties

50.00 @ 266nm **Effective Focal Length EFL (mm):**

0.25 **Numerical Aperture NA:**

46.26 **Back Focal Length BFL (mm):**

Calcium Fluoride (CaF<sub>2</sub>) Vacuum UV Grade **Substrate:**

266 **Aspheric Design Wavelength (nm):**

M6 **Asphere Figure Error, RMS @ 632.8nm:**

Uncoated **Coating:**

60-40 **Surface Quality:**

2.00 **f#:**

94.99 **Abbe Number (v<sub>d</sub>):**

266 **Design Wavelength DWL (nm):**

200 - 7000 **Wavelength Range (nm):**

266 **Focal Length Specification Wavelength (nm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000 **Imported By:**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- 266nm or 4µm Design Wavelength Options
- High Transmission from 200nm to 7µm
- Diamond Turned for High Surface Accuracy
- Vacuum UV Grade CaF<sub>2</sub> Substrate

TECHSPEC® Calcium Fluoride (CaF<sub>2</sub>) Aspheric Lenses have high transmission from the ultraviolet (UV) through the infrared (IR), covering the wavelength range of 200nm to 7µm. Calcium fluoride's low index of refraction enables these diamond turned aspheric lenses to be integrated with minimal Fresnel reflection loss without an anti-reflection coating. Calcium fluoride also offers low solubility and superior hardness compared to other fluoride-based substrates, allowing for these aspheric lenses to be used in harsh environments. TECHSPEC Calcium Fluoride (CaF<sub>2</sub>) Aspheric Lenses are available in two designs; one for Nd:YAG, Excimer Laser, and other UV applications with a design wavelength of 266nm and the other for spectroscopic, mid-wave IR (MWIR) thermal imaging, and other IR applications with a design wavelength of 4µm.

Please contact us for Calcium Fluoride Aspheric Lenses with custom designs or coating options.

## Technical Information



## Compatible Mounts

---