

25mm Diameter Mid-Wave Infrared Polarizer



Stock **#85-264** **1 In Stock**

-

1

+

₹1,47,137

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,47,137 each
Qty 6+	₹1,18,254 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

20.8

Diameter (mm):

25.00

Thickness (mm):

5.00

Nanoparticle	Construction:
Optical Properties	
±20	Angle of Incidence (°):
>1,000:1 (1500-5000nm) >10,000:1 (2000-4500nm)	Extinction Ratio:
Soda Lime Float Glass	Substrate: ☐
60-40	Surface Quality:
35 (1500-5000nm) 65 (2000-4500nm)	Transmission (%):
<3λ per 10mm	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
±2	Polarization Axis Mark (%):
1500 - 5000	Wavelength Range (nm):
1 W/cm² (Continuous Block) 5 W/cm² (Continuous Pass)	Damage Threshold, By Design: ☐
Environmental & Durability Factors	
-20 to +120	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 1.5 – 5µm Wavelength Range
- Mounted for Easy Handling and System Integration
- Highly Durable Soda Lime Substrate

Featuring high contrast ratios and transmittances, Mid-Wave Infrared (MMIR) Polarizers are designed for applications operating in the 1.5 – 5µm wavelength range. Ideal for harsh environments, each MMIR polarizer is constructed of a dichroic glass substrate which provides a high resistance to UV radiation and chemicals, as well as an operating temperature of up to 400°C.