


TECHSPEC® 25mm Dia. x 60mm FL, NIR I Coated, Achromatic Lens



Stock **#22-492** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹11,310.00**

ADD TO CART

Qty 1-5
₹11,310.00
Qty 6+
₹9,048.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 52.96
Focal Length Specification Wavelength (nm): 880.00
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 12.00 ±0.20
Center Thickness CT 1 (mm): 8.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 36.27
Radius R₂ (mm): -33.80
Radius R₃ (mm): -248.86
Edge Thickness ET (mm): 9.46
Substrate: ☐ N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 2.4
Numerical Aperture NA: 0.21
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 600 - 1050

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View