

**TECHSPEC® 25mm Dia. x 75mm EFL, 1064nm V-Coat, Sapphire Aspheric Lens**



Sapphire Aspheric Lenses

Stock **#27-257** **5 In Stock**

⊖ 1 ⊕ MRP ₹2,51,216

📌 Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹2,51,216 each
Qty 6-10	₹2,13,887 each
Qty 11+	₹2,00,771 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Physical & Mechanical Properties**

25.00 +0/-0.1 **Diameter (mm):**

3 **Centering (arcmin):**

22.5 **Clear Aperture CA (mm):**

**Center Thickness CT (mm):**

3.40 ±0.10

**Bevel:**

0.5 x 45°

**Surface Roughness (□):**

40

**Poisson's Ratio:**

0.27

**Young's Modulus (GPa):**

435

## Optical Properties

**Effective Focal Length EFL (mm):**

75.00

**Numerical Aperture NA:**

0.17

**Back Focal Length BFL (mm):**

73.06

**Substrate:** □

Sapphire (Al<sub>2</sub>O<sub>3</sub>)

**Coating:**

1064nm V-Coat

**Coating Specification:**

R<sub>abs</sub> < 0.25% @ 1064nm @ 0° AOI

**Surface Quality:**

40-20

**f/#:**

3

**Design Wavelength DWL (nm):**

1064

**Index of Refraction (n<sub>d</sub>):**

1.77

**Irregularity (P-V) @ 632.8nm:**

0.5λ

**Coating Aperture (mm):**

22.5

**Power (P-V) @ 632.8nm:**

1λ

## Material Properties

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

8.8

**Density (g/cm<sup>3</sup>):**

3.97

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 235:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Durable Sapphire Substrates Ideal For Material Processing and Advanced Manufacturing
- Uncoated and 1064nm Laser Line V-Coated Versions Available
- Diffraction Limited Performance at 1064nm

Sapphire Aspheric Lenses are designed for precision performance in high power applications. Utilizing durable sapphire substrates, these lenses decrease contamination effects on laser performance and feature better thermal conductivity, lower thermally induced focal shift, and faster induced focal shift rise time than fused silica. Designed with material processing and advanced manufacturing in mind, their aspheric surfaces provide diffraction limited performance at 1064nm. Sapphire Aspheric lenses are available uncoated, with a standard laser v-coat, or with custom coatings [available](#) upon request.

**Note:** Exercise caution when using Sapphire Aspheric Lenses in ultrafast laser applications as sapphire can cause non-linear effects.