

TECHSPEC® 25mm Diameter x 15mm Length, Cage Extension Tube



25mm Diameter x 15mm Length, Cage Extension Tube, #85-519

Stock **#85-519** 20+ In Stock

-

1

+

₹2,512

ADD TO CART

Volume Pricing	
Qty 1+	₹2,512 each
Need More?	Request Quote

Product Downloads

General

Fixed	Function:
Fixed Tube	Note:

Physical & Mechanical Properties

25.0	Compatible Plate Inner Diameter (mm):
15.00	Length (mm):

25.0	Outer Diameter (mm):
Black Anodized Aluminum	Construction:
25 Dia.	Dimensions (mm):
Threading & Mounting	
M23.2 x 0.75	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Fit within Inner Diameter of [Cage System Plates](#)
- Use with Retaining Ring Pairs to Secure Optics
- Join Multiple with Adjustable Length Tubes and Thread Adapters

TECHSPEC® M23.2 and M27.5 Fixed Tubes and Retaining Rings feature black anodized aluminum construction. The fixed extension tubes are ideal for covering portions of the cage system. Each fixed extension tube is designed to fit within the inner diameter of a cage system plate, and feature either M23.2 x 0.75 or M27.5 x 0.75 female threading throughout the entire length of the tube. TECHSPEC® M23.2 and M27.5 Fixed Tubes and Retaining Rings, when paired correctly, can be used to secure optics within the extension tube, while [adjustable length tubes](#) and [thread adapters](#) can be used to connect fixed extension tubes for building customized optical assemblies. M23.2 and M27.5 Tube System Retaining Rings feature a thin, 3mm thickness. They are sold in pairs and are ideal for securing optics within extension tubes. Each retaining ring features an optic shelf which centers the optic within when sandwiched between retaining ring pairs.

Accessories

[#85-582](#) threads into a M23.2 x 0.75 standard tube to easily mount a plate beamsplitter. [#85-539](#) fits within the inner diameter of [cage system plates](#); it also threads into a M23.2 x 0.75 standard tube.