

[See all 27 Products in Family](#)

TECHSPEC®

25mm Dia. x 75mm FL, 3 - 5µm Coated, Si Plano-Convex Lens



Stock **#69-687** 7 In Stock

[Other Coating Options](#)

-

1

+

₹31,141

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹31,141 each
Qty 6-25	₹24,894 each
Qty 26-49	₹23,333 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.1

Diameter (mm):

Centering (arcmin):

<3	
3.00 ±0.10	Center Thickness CT (mm):
2.57	Edge Thickness ET (mm):
24	Clear Aperture CA (mm):
Protective as needed	Bevel:
Optical Properties	
75.00 @ 10.6µm	Effective Focal Length EFL (mm):
74.12	Back Focal Length BFL (mm):
BBAR (3000-5000nm)	Coating:
R _{avg} <3.0% @ 3 - 5µm	Coating Specification:
Silicon (Si)	Substrate: □
60-40	Surface Quality:
2λ	Power (P-V) @ 632.8nm:
λ/2	Irregularity (P-V) @ 632.8nm:
181.32	Radius R ₁ (mm):
3.00	f/#:
0.17	Numerical Aperture NA:
3000 - 5000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Wavelength Range of 1.2 - 7µm
- Low Density and Dispersion
- Focal Lengths of 25 – 250mm Available
- Additional [Infrared Lenses](#) Available in Popular Substrates

Our TECHSPEC® Silicon Plano-Convex (PCX) Lenses feature precision polished surfaces, making them ideal for a variety of infrared applications, including Near-Infrared (NIR) imaging, and infrared spectroscopy. Available in a variety of focal lengths from f/1 thru f/10, the lenses are offered uncoated or broadband anti-reflection coated. For more information on Silicon properties, please review our guide to selecting [The Correct Material for Infrared \(IR\) Applications](#).

Technical Information



Compatible Mounts

;