

TECHSPEC[®] 25mm Dia. x 75mm FL 633nm V-Coat, UV PCX Lens



Stock #34-119 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹13,485.00

ADD TO CART

Qty 1-5
₹13,485.00
Qty 6+
₹10,788.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
75.00 @ 587.6nm

Back Focal Length BFL (mm): 71.96
Coating: Laser V-Coat (633nm)
Coating Specification: R _{abs} <0.25% @ 633nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 4.43 ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁ (mm): 34.39
Clear Aperture CA (mm): 24
f/#: 3.00
Numerical Aperture NA: 0.17
Design Wavelength DWL (nm): 633
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 633nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant