

[See all 76 Products in Family](#)

TECHSPEC® 25mm, f/1.4 Ci Series Fixed Focal Length Lens



25mm Focal Length

Stock #85-355 **20+ In Stock**

⊖ 1 ⊕ MRP ₹15,171

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹15,171 each
Qty 25+	₹13,659 each
Need More?	Request Quote

Product Downloads

General

Ci Series **Product Family:**

Fixed Focal Length Lens **Type:**

Compact Lens with Fixed Aperture **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed	Iris Option:
29.90	Length (mm):
26.5	Maximum Diameter (mm):
26.5	Outer Diameter (mm):
28	Weight (g):
1.33	Maximum Rear Protrusion (mm):
26.50	Diameter (mm):

Optical Properties

35mm - 19.8°	Horizontal Field of View @ Max Sensor Format:
Horizontal: 33.3mm - 19.8° Vertical: 24.9mm - 14.9° Diagonal: 41.8mm - 24.6°	Field of View at Max Sensor Format:
35mm - 19.8°	Horizontal Field of View, 2/3" Sensor:
28.5mm - 16.1°	Horizontal Field of View, 1/1.8" Sensor:
25.4mm - 14.5°	Horizontal Field of View, 1/2" Sensor:
22.6mm - 12.9°	Horizontal Field of View, 1/2.5" Sensor:
19mm - 10.9°	Horizontal Field of View, 1/3" Sensor:
14.2mm - 8.2°	Horizontal Field of View, 1/4" Sensor:
11.00	Maximum Image Circle (mm):
0.0766	Numerical Aperture NA, Object Side:
7 (6)	Number of Elements (Groups):
25.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.4	Aperture (f/#):
425 - 675nm BBAR	Coating:
425 - 675nm BBAR	Coating Specification:
15.89	Entrance Pupil Position (mm):
18.77	Object Space Principal Plane (mm):
-12.44	Image Space Principal Plane (mm):
0.21	Maximum Distortion (%):
-15.68	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M25.5 x 0.50 (Male)	Filter Thread:
#89-941 (Required)	Filter Thread Adapter:

Front Thread:
M22.0 x0.75 (Male)

Mount:
C-Mount

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized $f\#$ versions to best suit your instrumentation application needs and to discuss volume requirements, please [contact us](#).

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8 μ m Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- **Ruggedized (Cr) Designs** Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a **VIS-NIR Broadband Anti-Reflection (BBAR) Coating**.
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 and IPX9K.


Technical Information




#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Distortion Plot




#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Relative Illumination Plot




#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f1.4



#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f1.4



#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f1.4



#85-355, 25mm, f/1.4 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f1.4

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm

50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm

Compatible Cameras

;