

TECHSPEC[®] 25mm Dia x -100mm FL VIS 0°, Inked, Negative Achromatic Lens



Stock #62-494-INK 17 TO 22 D= DAYS

[Other Coating Options](#)

-

1

+

₹10,788.00

ADD TO CART

Qty 1-5

₹10,788.00

Qty 6+

₹9,179.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
-100.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : -102.37
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.57 ±0.20
Center Thickness CT 1 (mm) : 2.00 ±0.10
Center Thickness CT 2 (mm) : 2.57 ±0.10
Radius R₁ (mm) : -70.57
Radius R₂ (mm) : 45.27
Radius R₃ (mm) : 412.67
Edge Thickness ET (mm) : 5.81
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 4.00
Numerical Aperture NA : 0.13
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Negative Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View