

TECHSPEC[®] 25mm Dia. x -25mm FL, MgF₂ Coated, Double-Concave Lens



Stock #32-993 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹3,350.00

ADD TO CART

Qty 1-9
₹3,350.00
Qty 10+
₹3,023.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-25.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: MgF₂ (400-700nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -25.69
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.0
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 6.05
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -39.78
Surface Quality: 40-20
Damage Threshold, By Design: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant