

TECHSPEC<sup>®</sup>

25mm H x 50mm L x -150mm FL VIS-NIR Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC<sup>®</sup> Illumination Grade PCV Cylinder Lenses

Stock **#69-850** **2 In Stock**

-

1

+

₹10,198

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,198 each                  |
| Qty 6-25       | ₹9,186 each                   |
| Qty 26-49      | ₹8,719 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Cylinder Lens, Plano-Concave

Physical & Mechanical Properties

Center Thickness CT (mm):

4.00

Center Thickness Tolerance (mm):

|             |                             |
|-------------|-----------------------------|
| ±0.1        |                             |
| +0.0/-0.2   | Dimensional Tolerance (mm): |
| 25.0 x 50.0 | Dimensions (mm):            |
| 4.97        | Edge Thickness ET (mm):     |

Optical Properties

|                                                                                                                    |                                                       |
|--------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| -150.00                                                                                                            | Effective Focal Length EFL (mm):                      |
| N-BK7                                                                                                              | Substrate: <input type="checkbox"/>                   |
| VIS-NIR (400-1000nm)                                                                                               | Coating:                                              |
| 400 - 1000                                                                                                         | Wavelength Range (nm):                                |
| -152.64                                                                                                            | Back Focal Length BFL (mm):                           |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm | Coating Specification:                                |
| ±3                                                                                                                 | Focal Length Tolerance (%):                           |
| -77.52                                                                                                             | Radius R <sub>1</sub> (mm):                           |
| 60-40                                                                                                              | Surface Quality:                                      |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns                                                                                  | Damage Threshold, By Design: <input type="checkbox"/> |


Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 235:                  |
| China                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
  - Circular and Rectangular Form Factors
  - Multiple Coating Options Available
- TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.
- The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

Technical Information



Coating Curves

# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).