

TECHSPEC® 25mm λ /20, 266nm V-Coat, Nd:YAG Right Angle Prism



TECHSPEC Nd:YAG Laser Line λ /20 UV Fused Silica Right Angle Prisms

Stock **#37-621** 10 TO 12 DAYS

- 1 + **₹33,408.00**

ADD TO CART

Qty 1-5
₹33,408.00
Qty 6+
₹26,709.00
Volume Pricing
Request Quote

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (266nm)

Design Wavelength DWL (nm):
266

Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R _{abs} <0.25% @ 266nm
Surface Flatness (P-V): λ/20
Damage Threshold, By Design: ☐ 3 J/cm ² , 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View