

[See all 195 Products in Family](#)

**TECHSPEC® 25mm Diameter x 150mm FL, 1064nm Coated, Laser Grade PCX Lens**



TECHSPEC Laser Grade PCXLenses

Stock **#67-977 6 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹16,271

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹16,271 each
Qty 6-25	₹13,001 each
Qty 26-49	₹11,911 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.10 **Diameter (mm):**

**Centering (arcmin):**

<1

Center Thickness CT (mm):

3.18 ±0.10

Edge Thickness ET (mm):

2.04

Clear Aperture CA (mm):

22.5

Bevel:

Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):

150.00 @ 587.6nm

Back Focal Length BFL (mm):

147.82

Coating:

Laser V-Coat (1064nm)

Coating Specification:

$R_{\text{abs}} < 0.25\%$  @ 1064nm

Substrate:

[Fused Silica](#) (Corning 7980)

Surface Quality:

20-10

Power (P-V) @ 632.8nm:

$\lambda$

Irregularity (P-V) @ 632.8nm:

$\lambda/10$

Focal Length Tolerance (%):

±1

Radius  $R_1$  (mm):

68.79

f#:

6.00

Numerical Aperture NA:

0.08

Design Wavelength DWL (nm):

1064

Damage Threshold, By Design:

15 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

REACH 201:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

Singapore

Imported By:

Edmund Optics India Private Limited

## Product Details


- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- $\lambda/10$  Surface Accuracy

TECHSPEC® Laser Grade PCXLenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring  $\lambda/10$  surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.


**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information



**1064nm V-Coat**  
 $R_{(abs)} < 0.25\% @ 1064nm$



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts