


25mm Sq., Extended Hot Mirror



Extended Hot Mirrors

Stock #46-387 **13 In Stock**

₹5,294

ADD TO CART

Volume Pricing	
Qty 1-9	₹5,294 each
Qty 10-25	₹4,749 each
Qty 26-49	₹4,515 each
Need More?	Request Quote

Product Downloads

General

Shortpass Filter Type:

Physical & Mechanical Properties

3.30 ±0.2 Thickness (mm):

25.0 x 25.0 Dimensions (mm):

Clear Aperture (%):

≥85

Dimensional Tolerance (mm):

±0.5

Edges:

Seamed

Length (mm):

25.00

Width (mm):

25.00

Optical Properties

Coating Type:

Dielectric

Coating:

Hot Mirror, 0°

Surface Flatness (P-V):

4 - 6λ

Wavelength Range (nm):

425 - 1600

Substrate:

BOROFLOAT®

Angle of Incidence (°):

0.00

Coating Specification:

R_{avg} ≥90% @ 750 - 1150nm

R_{avg} ≥80% @ 1200 - 1600nm

T_{avg} ≥85% @ 425 - 675nm

Surface Quality:

80-50

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited


Product Details


- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information





Quote Your Size

Compatible Mounts