


**TECHSPEC® 25mm Diameter x 40mm EFL Aspherized Achromatic Lens**



Aspherized Achromatic Lenses



Stock **#49-664** 10 TO 12 DAYS



1



**₹13,659.00**

ADD TO CART

Qty 1-5

₹13,659.00

Qty 6+

₹10,919.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Diameter (mm):**  
25.00 +0.00/-0.05

**Effective Focal Length EFL (mm):**  
40.00

**Back Focal Length BFL (mm):**

|                                                                                               |
|-----------------------------------------------------------------------------------------------|
| 33.23                                                                                         |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                   |
| <b>Clear Aperture CA (mm):</b><br>23.00                                                       |
| <b>Centering (arcmin):</b><br>≤5                                                              |
| <b>Center Thickness CT (mm):</b><br>11.58                                                     |
| <b>Center Thickness CT 1 (mm):</b><br>9.00                                                    |
| <b>Center Thickness CT 2 (mm):</b><br>2.58                                                    |
| <b>Radius R<sub>1</sub> (mm):</b><br>24.80                                                    |
| <b>Radius R<sub>2</sub> (mm):</b><br>37.60                                                    |
| <b>Radius R<sub>3</sub> (mm):</b><br>102.34                                                   |
| <b>Edge Thickness ET (mm):</b><br>7.54                                                        |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SK14</a> / <a href="#">N-SF57</a> |
| <b>Surface Quality:</b><br>60-40, glass surfaces only                                         |
| <b>f/#:</b><br>1.6                                                                            |
| <b>Numerical Aperture NA:</b><br>0.31                                                         |
| <b>Coating:</b><br>VS 0° (425-675nm)                                                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                         |
| <b>Note:</b><br>VS 0° Coating on First Surface, Second Surface is Aspheric Polymer            |
| <b>Operating Temperature (°C):</b><br>-20°C to 80°C                                           |
| <b>Type:</b><br>Achromatic Lens                                                               |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |