

25mW, 850nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock #19-454 **2 In Stock**

1 MRP ₹27,931

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹27,931 each
Qty 10+	₹25,138 each
Need More?	Request Quote

Product Downloads



General

IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

36.00 **Length (mm):**

Optical Properties

Wavelength (nm):

850.00

Wavelength Tolerance (nm):

±5

Beam Diameter (mm):

3.5 typical

Beam Divergence (mrad):

<1.0

Color:

infrared

Electrical

Output Power (mW):

25

Modulation Frequency (kHz):

0 - 10

Hardware & Interface Connectivity

Operating Voltage (V):

5

Power Supply:

Power Supply Required and Sold Separately.

USA: [#73-818](#)

Europe: [#73-818](#)

Japan: [#13-640](#)

Korea: [#33-770](#)

China: [#73-818](#)

Environmental & Durability Factors

Operating Temperature (°C):

-10 to 50

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 233:

[Compliant](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Focus Adjustable
- TTL Modulation up to 10kHz
- 635nm, 780nm, 808nm, 850nm, and 980nm Wavelength Options

Red and IR Alignment Laser Diodes are available in output powers from 1 to 100mW at 635nm, 780nm, 808nm, 850nm, and 980nm wavelengths. These low cost laser diode modules combine drive electronics and beam collimating optics, making them ideal for OEM integration applications. Red and IR Alignment Laser Diodes feature TTL Modulation up to 10kHz and are best utilized in alignment applications or systems with simple detectors.

Note: Power supply and mounting bracket are sold separately.