

2.5X InfiniFlex HD Compact Lens

See More by [Infinity Photo-Optical Company](#)



Stock **#89-949** **2 In Stock**

-

1

+

₹81,450

ADD TO CART

Volume Pricing	
Qty 1+	₹81,450 each
Need More?	Request Quote

Product Downloads

General

Fixed Magnification Lens

Type:

Physical & Mechanical Properties

63.20

Length (mm):

15.0

Maximum Diameter (mm):

Optical Properties

2.6mm	Horizontal Field of View, 1/2" Sensor:
0.13	Numerical Aperture NA:
2.5X	Primary Magnification PMAG:
20.00	Working Distance (mm):

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

C-Mount	Mount:
---------	--------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Multiple Options Available by Combining Main Bodies and Amplifiers
- High Light Throughput and Resolution with 0.13 NA
- Standardized 20mm Working Distance

InfiniFlex™ HD Compact Lenses are high performance micro imaging lenses designed to maximize system resolution. These lenses support up to 2/3" format sensors and feature an easy-to-use, patent-pending design. Simply choose a main body and an optional amplifier to reach magnifications ranging from 2X to 12X. The 2XPLAN version is designed specifically for increased full field imaging. For applications requiring brightfield or darkfield illumination, a 21mm Ring Light Adapter is available and allows a ring light to be moved along the body of the 15mm diameter lens to permit full angular illumination. A retainer is also available for integrating a 20mm filter in between the lens and the camera. Because the InfiniFlex™ HD Compact Lenses share similar dimensions as the [InfiniStix™ Imaging Lenses](#), the two lenses can be used together to achieve high resolutions and increased depth of field.

Technical Information

