

260nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock #67-743 **2 In Stock**

1 MRP ₹17,656

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹17,656 each
Qty 10-25	₹15,941 each
Qty 26-49	₹15,134 each
Need More?	Request Quote

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Bandpass Filter	Typical Applications: General Filtering
------------------------------	--

Physical & Mechanical Properties

Diameter (mm): 12.50 +0.00/-0.25	Clear Aperture CA (mm): 9.0
Construction: Mounted in Black Anodized Ring	

Optical Properties

Angle of Incidence (°): 0	Optical Density OD (Average): ≥4.0
Center Wavelength CWL (nm): 260.00 +3.0/-0.0	Center Wavelength CWL Tolerance (nm): +3.0/-0.0
Full Width-Half Max FWHM (nm): 10.00 ±2	Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >12	Coating: Traditional Coated
Surface Quality: 80-50	Blocking Wavelength Range (nm): 200 - 10000

Threading & Mounting

Mount Thickness (mm): 3.5	
----------------------------------	--

Environmental & Durability Factors

Operating Temperature (°C): -50 to +50

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

REACH 241: [Compliant](#)

Country of Origin: United States

Imported By: Edmund Optics India Private Limited
267, Greystone Building,
Second Floor,
6th Cross Rd,
Binnamangala,
Stage 1,
Indiranagar,
Bengaluru,
Karnataka,
India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Available in UV, Visible, and IR Center Wavelengths
- 10 – 80nm Bandwidths Available
- Ideal for Biomedical Applications and Instrumentation Integration
- 193-399nm, [400-699nm](#), and [700-1650nm](#) CWL Options Available

Traditional Coated Bandpass 193 – 399nm Interference Filters are used to selectively transmit a narrow range of wavelengths while blocking all others. They are ideal for a range of biomedical and quantitative chemical applications. Bandpass interference filters are widely used in instrumentation for various applications, including clinical chemistry, environmental testing, colorimetry, elemental and laser line separation, flame photometry, fluorescence, and immunoassays. In addition, Traditional Coated Bandpass 193 – 399nm Interference Filters are used to select discrete spectral lines from arc or gas discharge lamps and to isolate a particular line from Ar, Kr, Nd:YAG, and other lasers. Traditional Coated Bandpass 193 – 399nm Interference Filters are often used in conjunction with [laser diode modules](#) and [LEDs](#).

Traditional Coated Filters

Traditional coated filters are fabricated in three sections, one of which determines the center wavelength (CWL), bandwidth (FWHM), and the shape of the transmittance curve while the other two control the blocking range of the filter. The bandpass section of Traditional Coated Bandpass Interference Filters is made by repetitive vacuum deposition of thin layers of partially reflecting dielectric compounds on a glass substrate. Rejection of wavelengths resulting from destructive interference is limited to within 15% of the central wavelength, therefore, additional glass or metallic blockers must be added to reduce out-of-band transmittance. Metallic blockers, such as layers of silver, reflect and absorb radiation outside of the filter passband and negate higher order passbands from X-ray to the long-wave infrared (LWIR). The blocking capabilities of metallic blockers are augmented by the addition of color transmitting glass and custom dyes that absorb UV or long wavelength radiation. After thin film deposition is complete, the three sections are scribed, laminated, cut, and mounted.

Technical Information

Related Products



Optic Component Mounts



C, S, and T-Mount Circular Optic Mounts



Cotton-Tipped Swab Applicators



Hard Coated OD 4.0 10nm Bandpass Filters

Frequently Purchased Together



#60-375 - 7.75" x 4" Sheets, Industrial Grade Lens Tissue
₹4,195



#67-737 - 232nm CWL, 10nm FWHM, 12.5mm Mounted Diameter
₹24,214



































#65-625 - 450nm CWL, 12.5mm Dia., 10nm FWHM, Interference Filter
₹10,594







#67-735 - 220nm CWL, 10nm FWHM, 12.5mm Mounted Diameter
₹24,214

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
MORE+	12.5/12.7mm Optic Dia., SM05 Thin Mount, M4	Fixed		#13-789	₹1,967 Request Quote	20+ In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	12.5/12.7mm Optic Dia., SM05 Thin Mount, 8-32	Fixed		#13-790	₹1,967 Request Quote	2 In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	12.5/12.7mm Optic Dia., E-Series Kinematic Mount	Adjustable - Tip-Tilt		#15-865	₹4,388 Request Quote	CONTACT US <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	12.5/12.7mm Optic Dia., L-Slot Direct Mount	Fixed		#36-416	₹5,953 Request Quote	1 In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	12.5/12.7mm Optic Dia., Side Flange Direct Mount	Fixed		#36-418	₹5,953 Request Quote	1 In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	2.0 - 35.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#03-668	₹6,357 Request Quote	20+ In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	9.5 - 73.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#36-605	₹8,374 Request Quote	CONTACT US <input type="text" value="1"/> <input type="button" value="🛒"/>
MORE+	12.5/12.7mm Optic Dia., Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#58-850	₹9,383 Request Quote	20+ In Stock <input type="text" value="1"/> <input type="button" value="🛒"/>

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	12.5/12.7mm Optic Dia., L-Slot and Rotation Direct Mount	Adjustable - Rotary		#36-417	₹9,736 Request Quote	12 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Compact Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#34-720	₹10,190 Request Quote	14 In Stock <input type="text" value="1"/> 
MORE+ 	5.0 - 25.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-529	₹10,291 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#58-853	₹10,493 Request Quote	14 In Stock <input type="text" value="1"/> 
MORE+ 	7.0 - 40.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-676	₹10,694 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	₹10,896 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	₹11,703 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Compact Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#34-721	₹11,805 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	₹12,107 Request Quote	10 In Stock <input type="text" value="1"/> 
MORE+ 	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	₹15,840 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Stainless Steel Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#26-814	₹16,244 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Stainless Steel Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#26-817	₹18,362 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-955	₹26,333 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Top Adjust Kinematic Mount, Lead Screw	Adjustable - Tip-Tilt		#13-768	₹27,240 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Top Adjust Kinematic Mount, Micrometer	Adjustable - Tip-Tilt		#13-769	₹29,158 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	₹41,365 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	12.5/12.7mm Optic Dia., Precision Gimbal Mount	Adjustable - Gimbal		#84-640	₹42,475 Request Quote	7 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-958	₹43,282 Request Quote	5 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Scientific Paper
- FAQ
- Glossary
- Video
- Published Article
- Trending in Optics

APPLICATION NOTE

The Importance of Optical Filter Orientation....

SCIENTIFIC PAPER

Ultraviolet fatigue testing of laser optics

APPLICATION NOTE

UV Optics: Tighter Tolerances and Different...

APPLICATION NOTE

Why Laser Damage Testing is Critical for UV...

? FAQ

Can BK7 be used for UV applications?

GLOSSARY

Ultraviolet (UV) Spectrum

[View More](#)