


27mm Diameter, English Hole Gauge, Contact Reticle



Hole Gauge

Stock **#39-456** CLEARANCE **2 In Stock**

-

1

+

₹6,255

ADD TO CART

Volume Pricing	
Qty 1-4	₹6,255 each
Qty 5-9	₹5,877 each
Qty 10+	₹5,598 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

English Hole Gauge

Type:

Physical & Mechanical Properties

27.00 ±0.05	Diameter (mm):
2.28 ±0.127	Thickness (mm):
±2	Line to Line Accuracy (µm):
Protective as needed	Bevel:
<30	Parallelism (arcsec):
0.25	Centering (mm):
25.00	Line Thickness (µm):
±13	Line Thickness Tolerance (µm):
Optical Properties	
±1	Angle Tolerance (arcsec):
60-40	Surface Quality:
3 - 4λ	Surface Flatness (P-V):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

English Scale: 0.01", 0.02", 0.03", 0.04", 0.05", 0.06", 0.07", 0.08", 0.09", 0.10", 1/64", 1/32", 1/16", 1/8", ¼" Hole Sizes.

- Greater Stability than Film Reticles
- Low Reflection Chrome Pattern
- Compatible with 6 or 9X Comparators

These glass reticles offer greater stability than film reticles which can bend, warp, and easily be damaged. Patterns are low reflection chrome deposition for high contrast and easy readability. Markings are on the outside of the reticle, so the scales are always in direct contact with the object under view. This provides optimum focus and accurate measurements. Our 21mm and 27mm diameter reticles for use with our [6X and 9X comparators](#) and our 26mm and 35mm diameter reticles for use with our [Peak Measuring Loupes](#) and our [Peak Illuminated Magnifiers](#). Please note the field of view specified for the magnifiers before selecting a magnifier/reticle combination. For example, the 5/8" (16mm) field of view for a 12X comparator may not be suitable for use with a reticle that has a ¾" (20mm) scale if the full scale is needed.