

TECHSPEC®

25mm H x 50mm L x 50mm FL VIS-NIR Coated, Illumination Grade PCX Cylinder Lens



Stock #69-784 **2 In Stock**

⊖ 1 ⊕ MRP ₹15,171

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹15,171 each
Qty 6-25	₹13,730 each
Qty 26-49	₹13,058 each
Need More?	Request Quote

Product Downloads

General

Cylinder Lens, Plano-Convex **Type:**

Physical & Mechanical Properties

Center Thickness CT (mm):
4.24

Center Thickness Tolerance (mm):

±0.1	Dimensional Tolerance (mm):
+0.0/-0.2	
	Dimensions (mm):
25.0 x 50.0	
	Edge Thickness ET (mm):
1.03	
Optical Properties	
	Effective Focal Length EFL (mm):
50.00	
	Substrate: <input type="checkbox"/>
N-BK7	
	f#:
2	
	Numerical Aperture NA:
0.25	
	Coating:
VIS-NIR (400-1000nm)	
	Wavelength Range (nm):
400 - 1000	
	Back Focal Length BFL (mm):
47.20	
	Coating Specification:
R _{abs} ≤ 0.25% @ 880nm	
R _{avg} ≤ 1.25% @ 400 - 870nm	
R _{avg} ≤ 1.25% @ 890 - 1000nm	
	Focal Length Tolerance (%):
±3	
	Radius R₁ (mm):
25.93	
	Surface Quality:
60-40	
	Damage Threshold, By Design: <input type="checkbox"/>
5 J/cm ² @ 532nm, 10ns	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	
	Country of Origin:
China	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details



- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

Note: For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).

Technical Information

Circular And Rectangular Cylinder Lenses



PCX Rectangular

Coating Curves