

[See all 14 Products in Family](#)

## 25mm Outer Dia., Zero Aperture, Stainless Steel Leaves



Zero Series

Stock #57-594 **5 In Stock**

⊖ 1 ⊕ MRP ₹11,805

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹11,805 each
Qty 5-9	₹10,432 each
Qty 10-25	₹9,645 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Maximum Aperture (mm):  
12.0

Outer Diameter (mm):  
25.0

Construction:  
Anodized Aluminum Alloy, Stainless Steel Leaves

Full Angular Range of Lever (°):

96.00	
3	<b>Lever Diameter (mm):</b>
12.00	<b>Lever Length (mm):</b>
2.50	<b>Lever Position (mm):</b>
Two sets of 6	<b>Number of Leaves:</b>
M1.4 x 0.30mm	<b>Pin Thread &amp; Pitch:</b>
5.00	<b>Thickness (mm):</b>

### Optical Properties

0.00	<b>Minimum Aperture (mm):</b>
------	-------------------------------

### Environmental & Durability Factors

<400	<b>Operating Temperature (°C):</b>
------	------------------------------------

### Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>Reach 247:</b>
Germany	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Iris Completely Closes
- Corrosion Resistant Housing
- High Heat Resistance
- Burnished Spring Steel and Stainless Spring Steel Leaf Options Available

High Performance Zero Aperture Series Iris Diaphragms provide optimum performance reliability even under the most extreme conditions. High quality materials combined with the highest fabrication guarantee their exceptional performance. Different leaf and aperture diameter options allow these irises to be successfully integrated into a variety of applications including imaging and high temperature environments. High Performance Zero Aperture Series Iris Diaphragms feature housing that is corrosion resistant with a matte finish and black anodized aluminum alloy. Known pin/tab angular deviation allows upfront, accurate assessment of movement requirements.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

Note: [Iris Diaphragm Mounts](#) sold separately.

## Technical Information

Outer Diameter A	Maximum Aperture B	Minimum Aperture C	Thickness D	Level Position E	Full Angular Range of Lever F	Stock No.
94mm	60mm	0mm	9mm	4.5mm	98°	<a href="#">#57-592</a> <a href="#">#57-599</a>
69mm	40mm		6.5mm	3.25mm	96°	<a href="#">#57-591</a> <a href="#">#57-598</a>
48mm	30mm		5mm	2.5mm	100°	<a href="#">#57-590</a> <a href="#">#57-597</a>
39mm	22mm		5mm	2.5mm	99°	<a href="#">#57-589</a> <a href="#">#57-596</a>
29mm	15mm		5mm	2.5mm	97°	<a href="#">#57-588</a> <a href="#">#57-595</a>
25mm	12mm		5mm	2.5mm	96°	<a href="#">#57-587</a> <a href="#">#57-594</a>
117mm	75mm		9.5mm	4.75mm	97°	<a href="#">#57-593</a> <a href="#">#57-600</a>

**High Performance Iris Diaphragms**

