

TECHSPEC[®] 2mm Diameter 45° Rod Mirror Aluminum Coated



45° Rod Mirrors

Stock #54-092 20+ In Stock

-

1

+

₹9,900

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,900 each
Qty 6-25	₹8,910 each
Qty 26-49	₹7,920 each
Need More?	Request Quote

Product Downloads

General	
Rod Lens	Type:
Coating on Elliptical Surface	Note:
Physical & Mechanical Properties	
2.00 +0.00/-0.05	Diameter (mm):

4.00	Length (mm):
Protective as needed	Bevel:
±0.1	Length Tolerance (mm):
Optical Properties	
Protected Aluminum (400-700nm)	Coating:
N-BK7	Substrate: ☐
40-20	Surface Quality:
±10	Angle Tolerance (arcmin):
R _{avg} >85% @400 - 700nm	Coating Specification:
90	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
Metal	Coating Type:
0.3 J/cm ² @ 532nm & 1064nm, 10ns	Damage Threshold, By Design: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 251:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Protected Aluminum Coating
- Reflect Light at 90°

TECHSPEC® 45° Rod Mirrors are designed for use in a variety of laser and imaging systems. The mirrors can be used to redirect laser light at 90°. Their small diameters make them ideal for use in fiberscope/borescope applications where size is critical. TECHSPEC 45° Rod Mirrors feature polished elliptical surfaces and ground circumferences and bases. These components are available in a range of micro sizes for integration into a host of OEM applications.

Technical Information

