

TECHSPEC® 25mm Sq., 2mm Thick, Uncoated λ/4 N-BK7 Window



Stock #20-573 10 TO 12 DAYS

⊖ 1 ⊕ **₹5,568**

ADD TO CART

Qty 1-5

₹5,568

Qty 6+

₹4,459

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
22.50 x22.50

Dimensions (mm):
25.00 x25.00 +0.00/-0.25

Thickness (mm):
2.00 ±0.20

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
7.1 (-30 to +70°C)
8.3 (+20 to +300°C)

Density (g/cm³):
2.51

Edges:
Fine Ground

Index of Refraction n_d:
1.516

Knoop Hardness (kg/mm²):
610

Parallelism (arcmin):
<1

Poisson's Ratio:
0.206

Substrate:
[N-BK7](#)

Surface Quality:
60-40

Transmitted Wavefront, P-V:
λ/4

Type:
Protective Window

Wavelength Range (nm):
350 - 2200

Young's Modulus (GPa):
82

Length (mm):
25.00

Width (mm):
25.00

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)