

[See all 2 Products in Family](#)

25mm Standard UV Fixed Focal Length Lens



25mm Standard UV Fixed Focal Length Lens, #57-542

Stock #57-542 **3 In Stock**

1 **MRP ₹2,07,924**

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,07,924 each
Need More?	Request Quote

Product Downloads

General

UV Fixed Focal Length Lenses **Product Family:**

Fixed Focal Length Lens **Type:**

Physical & Mechanical Properties

Variable **Iris Option:**

25.40 **Length (mm):**

30.0	Maximum Diameter (mm):
30	Outer Diameter (mm):
33.00	Weight (g):

Optical Properties

58.9	Field of View @ Min Working Distance (mm):
58.9mm - 14.0°	Horizontal Field of View, 1/2" Sensor:
16.00	Maximum Image Circle (mm):
25.00	Focal Length FL (mm):
230 - ∞	Working Distance (mm):
f/2.8 - f/16	Aperture (f#):
UV-NIR	Lens Wavelength Range:

Sensor

1"	Maximum Sensor Format:
----	------------------------

Threading & Mounting

M25.5 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- 1", C-Mount Lens
- Spectral Range of 230 - 1200nm
- 25mm to 78mm Focal Lengths

UV Fixed Focal Length Lenses are ideal for use in a variety of applications, including the surface inspection of circuits or fiber optics, quality control of semiconductor materials, or for locating oil contamination or leakage. Additional applications include forensic, pharmaceutical, or biomedical imaging, fluorescence, security, or counterfeit detection. UV Fixed Focal Length Lenses are manufactured from fused silica elements to provide excellent transmission from the ultraviolet to the near-infrared.

Note: These lenses are not corrected for chromatic aberration, and require refocusing when using an illumination source with a spectral bandwidth greater than 10nm. A monochromatic light source and narrow bandpass filter are recommended to improve the overall performance of the lens. The 78mm lens ([#57-543](#)) has a removable C-mount adapter, enabling it to be used with M42 x 0.75 (T2) mounts.

Technical Information



