

**TECHSPEC® 266nm CWL, 12.5mm Dia., Hard Coated OD 4.0 5nm Bandpass Filter**



TECHSPEC Hard Coated OD 4.0 5nm Bandpass Filters

Stock **#39-327** 10 TO 12 DAYS  
[Additional Bandwidths](#)

⊖ 1 ⊕ **₹18,531.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹18,531.00                    |
| Qty 6+                        |
| ₹14,834.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
12.50 +0.0/-0.1

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

|                                                                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>8.5                                                                                                                                               |
| <b>Center Wavelength CWL (nm):</b><br>266.00 ±1.0                                                                                                                                   |
| <b>Full Width-Half Max FWHM (nm):</b><br>5.00 ±1.0                                                                                                                                  |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Coming 7980)                                                                                            |
| <b>Minimum Transmission (%):</b><br>>55                                                                                                                                             |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                      |
| <b>Surface Quality:</b><br>80-50                                                                                                                                                    |
| <b>Type:</b><br>Bandpass Filter                                                                                                                                                     |
| <b>Typical Applications:</b><br>4th Harmonic Nd:YAG Laser                                                                                                                           |
| <b>Blocking Wavelength Range (nm):</b><br>200 - 650                                                                                                                                 |
| <b>Construction:</b><br>Mounted in Black Anodized Ring                                                                                                                              |
| <b>Environmental Durability:</b><br>Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7                                               |
| <b>Physical Durability:</b><br>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497A Section 4.5.4.2 |
| <b>Mount Thickness (mm):</b><br>5.0 ±0.1                                                                                                                                            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |